


Parasitic Extraction for Inductance Calibre xL



Parasitic inductance (noise, distortion, impedance mismatch and jitter) can cause chip failure if not accounted for in parasitic extraction. At higher frequencies, inductance can shift the frequency of oscillation in a VCO (lower graphic) and must be taken into account.

Managing Inductive Effects in Nanometer Designs

With increasing operating frequencies, interconnect lines begin to exhibit inductive effects that can significantly influence chip behavior and performance. Parasitic on-chip inductance extraction is crucial for accurate physical verification (simulation) and timely tape-out of high-frequency RF, mixed-signal, and custom digital nanometer designs.

Calibre® xL offers designers full-chip, fast, and accurate extraction of frequency-dependent loop inductance and loop resistance, and automatically accounts for return path change with frequency. Results of Calibre xL extraction highly correlate with field solvers and have silicon-tested accuracy.

Calibre xL Inductance Solution

On-chip inductance modeling is challenging because inductive couplings are long-range, and the return paths for the current are frequency-dependent and difficult to determine or predict. A partial inductance approach, which does not require knowledge of the current return path, results in prohibitively large and dense inductance matrices for any reasonable size design and produces netlists that are unmanageable for today's dynamic simulators.

The Calibre xL inductance calculation engine has a unique, accurate, and efficient way of calculating self-loop inductances in complex designs. Automated reduction of model order reduces parasitic R, C, and L data and produces a passive, realizable network for easy and efficient simulation, with no significant loss in accuracy.

BENEFITS:


- Full-chip, high-performance, parasitic inductance extraction provides highly correlated field solver and silicon-tested accuracy for analog, RF, and custom digital nanometer designs.
- Powerful mutual inductance engine enables extraction of the effect of coupling between different nets.
- Parasitic self-inductance extraction integrated with Calibre xRC parasitic RC extraction data enables accurate analysis of high frequency effects in nanometer technology.
- Accurate extraction of frequency dependent loop inductance and resistance ensures optimized modeling of on-chip physical effects.
- Efficient, realizable model order (RLC) reduction provides manageable netlists and mixed-level outputs for ease of re-simulation without loss of accuracy.
- Return-path selection and net-based extraction frequency selection offers increased flexibility in performance and improved accuracy.
- Seamless invocation, and integration to Calibre LVS, xRC, xACT 3D, and RVE, through Calibre Interactive enables cross-probing and debugging of results in popular layout environments.

Calibre xL's filtering engine eliminates inductively unimportant wires from the inductance extraction flow, additionally improving accuracy and simulation performance. Its powerful mutual inductance engine allows the designer to extract the effect of coupling between different bundles. The use model for this feature is victim-based, meaning that only victim nets are selected, and Calibre xL then automatically finds the aggressors within a specified area.

Calibre xL offers unprecedented flexibility through selected net extraction, automatic and customizable selection of the return path, net-by-net base frequency selection, and single run multiple frequency inductance extraction, with no need for calibration. Calibre xL has the performance to handle full-chip extraction for microprocessor designs, and the accuracy for analog/RF designs.

Calibre Design Platform and Flow Integration

Calibre xL is fully integrated into the Calibre flow and with popular design environments. It offers designers inductance extraction independent of design style and flow. For analog/RF blocks, it provides necessary accuracy; for digital designs, it provides high capacity and performance.



Calibre xL is fully integrated with Calibre LVS, xRC, and xACT 3D for complete circuit netlist information and back-annotation.

Calibre xL extends the capability of Calibre xRC and Calibre xACT 3D, the full-chip, industry-proven parasitic extraction solution from Mentor Graphics. By reading Calibre LVS data structures directly, Calibre xRC or Calibre xACT 3D works with Calibre xL to provide complete circuit netlist information integrated to the source schematic for back-annotation.

Supported Platforms

32- and 64-bit Linux Redhat and Sun Solaris.

Superior Product Support

Mentor Graphics is a five-time winner of the Software Technical Assistance Recognition (STAR) Award in EDA. No other provider of complex software can match the support offered by Mentor Graphics.



For the latest product information, call us or visit: www.mentor.com

©2011 Mentor Graphics Corporation, all rights reserved. This document contains information that is proprietary to Mentor Graphics Corporation and may be duplicated in whole or in part by the original recipient for internal business purposes only, provided that this entire notice appears in all copies. In accepting this document, the recipient agrees to make every reasonable effort to prevent unauthorized use of this information. All trademarks mentioned in this document are the trademarks of their respective owners.

Corporate Headquarters
Mentor Graphics Corporation
 8005 SW Boeckman Road
 Wilsonville, OR 97070-7777
 Phone: 503.685.7000
 Fax: 503.685.1204
Sales and Product Information
 Phone: 800.547.3000
sales_info@mentor.com

Silicon Valley
Mentor Graphics Corporation
 46871 Bayside Parkway
 Fremont, CA 94538 USA
 Phone: 510.354.7400
 Fax: 510.354.7467
North American Support Center
 Phone: 800.547.4303

Europe
Mentor Graphics
Deutschland GmbH
 Arnulfstrasse 201
 80634 Munich
 Germany
 Phone: +49.89.57096.0
 Fax: +49.89.57096.400

Pacific Rim
Mentor Graphics (Taiwan)
 Room 1001, 10F
 International Trade Building
 No. 333, Section 1, Keelung Road
 Taipei, Taiwan, ROC
 Phone: 886.2.87252000
 Fax: 886.2.27576027

Japan
Mentor Graphics Japan Co., Ltd.
 Gotenyama Garden
 7-35, Kita-Shinagawa 4-chome
 Shinagawa-Ku, Tokyo 140-0001
 Japan
 Phone: +81.3.5488.3033
 Fax: +81.3.5488.3004

